High Power 3 µm DPSSL Modules





Specifications

	DPM-2 (Er:YAG) free / fiber ^[1]	DPM-25 (Er:YAG) free / fiber ⁽¹⁾	DPM-50 (Er:YAG) free / fiber
Optical Parameters			
. Wavelength	2940 nm	2940 nm	2940 nm
 Average Output Power (max) 	2 / 1.2 W	25 / 16 W	50 / 33 W
Pulse Energy (max)	20 ^[2] / 13 ^[2] mJ	300 ^[2] / 200 ^[2] mJ	600 ^[2] / 400 ^[2] mJ
Pulse Repetition Rate	up to 1 kHz	up to 1 kHz	up to 1 kHz
Pulse Duration	40 to 1000 ⁽³⁾ µs	40 to 1000 ⁽³⁾ µs	40 to 1000 ⁽³⁾ µs
Average Current (max)	30 A	25 A	25 A
Mode of Operation	Pulsed	Pulsed	Pulsed
 Efficiency (optical-optical) 	> 10 %	> 10 %	> 10 %
Beam Shape (focus)	top hat like	top hat like	top hat like
Free Beam Quality	M ² < 5	M ² < 25	M ² < 50
Free Beam Diameter	0.6 mm	1.6 mm	1.6 mm
 Free Divergence (half angle) 	< 25 mrad	< 25 mrad	< 50 mrad
 Fiber Diameter GeO2 ⁽¹⁾ 	~ 230 µm (NA < 0.2)	~ 230 µm (NA < 0.2)	~ 420 µm (NA < 0.2)
Cooling Requirements			
Coolant	Distilled water with Algaecide	Distilled water with Algaecide	Distilled water with Algaecide
	and Corrosion Inhibitor	and Corrosion Inhibitor	and Corrosion Inhibitor
Coolant Temperature	20 to 35 °C	20 to 25 °C	20 to 25 °C
Coolant Flow Rate	≥ 1 lpm	> 5 lpm	≥ 6 lpm
Coolant Pressure	(1 - 3) bar	(2 - 5) bar	(3 - 5) bar
 Required Cooling Power 	~ 150 W @ 25 °C Environment	≥ 540 W @ 25 °C Environment	≥ 780 W @ 25 °C Environmen
	Temperature	Temperature	Temperature
Electrical Parameters			
 Diode Forward Voltage 	2 V	~ 20 V	~ 30 V
 Diode Forward Current 	350 A Pulsed	300 A Pulsed	300 A Pulsed
 Average Power Consumption (max) 	< 120 W incl. 2 TECs	< 450 W	< 900 W
Mechanical Dimensions			
. W x D x H	30 x 32 x 25 mm	120 x 96 x 75 mm	120 x 120 x 75 mm
. Weight	60 g	1.5 kg	1.7 kg
Emission Height	-	47.5 mm	47.5 mm

⁽¹⁾ Fiber as specified by Pantec

⁽²⁾ For pulse durations > 600 µs

 $^{\scriptscriptstyle (3)}$ 600 μs standard, 1000 μs on request



Laser Diode Drivers

The LDD series are economic QCW laser diode driver modules designed to provide high current pulses to drive 3m.i.k.r.o.n.™ modules in various applications. It delivers output currents up to 300 A and pulse widths variable from 50 up to 1000⁽³⁾ µs operation. Up to 1000 W average output power is available with the supplied heatsink and forced air flow. Several safety features are integrated to protect both laser diode and driver.

	DPM-2 (Er:YAG) / DPM-25 (Er:YAG)	DPM-50 (Er:YAG)	
Laser Diode Driver	LDD-20300	LDD-30300	
 Output Current 	up to 300 A	up to 300 A	
 Rise Time (10 - 90%) 	< 20 µs	< 20 µs	
 Mechanical Dimensions (W x D x H) 	200 x 150 x 85 mm	200 x 150 x 85 mm	
 Additional Features 	Safety circuit and	Safety circuit and	
	communication interface	communication interface	

Test and Evaluate



The 3m.i.k.r.o.n.TM evalution kits are ready-to-use and straightforward laboratory systems for first feasibility studies in research environment. The evaluation kits are available with three different kind of laser sources (see front page), shortens the development time, enables flexibility and a fast demonstration of feasibility. The test systems are delivered with your requested laser source, a laser control system and a cooling system for laboratory use only.

Please contact us for more information on rental or purchase conditions: 3um@pantec.com

3m.i.k.r.o.n.™ Applications

Medical	

- . Aesthetics / Dermatology
- Dentistry
- . ENT
- Lithotripsy
- . Minimally-Invasive Surgery
- Orthopedicsetc.

More Services



Customized laser sources Optical and mechanical design Contract development and manufacturing Medical device consulting (IP research, Medical CE, ...)





Pantec Biosolutions AG · Medical Laser Industriering 21 · 9491 Ruggell · Liechtenstein Tel: +423 377 13 33 · Fax: +423 377 13 34 info@pantec-biosolutions.com www.pantec-biosolutions.com

Illustrations, descriptions and technical data are not binding and may be changed without notice. Copyright Pantec Biosolutions AG, Ruggell, Liechtenstein, 2022 – All rights reserved.



- . Material Processing (Drilling, Cutting, Melting, Welding, Evaporation)
- Analytics
- . Security
- Defense